

## MRL-FN-671/1~1000mW



### LD PUMPED ALL-SOLID-STATE RED LASER AT 671nm

DPSS red laser at 671nm is made features of ultra compact, long lifetime, high stability and easy operating, which is widely used in measurement, spectrum analysis, and scientific research etc.



### SPECIFICATIONS

Wavelength (nm)	671±1	
Operating mode	CW	
Output power (mW)	>1, 10, 100, ... , 400	>400, ... , 1000
Power stability (rms, over 4 hours)	<1%, <2%, <3%	<2%, <3%
Transverse mode	TEM <sub>00</sub>	
M <sup>2</sup> factor	<1.2 (<1.1 optional)	<1.2
Beam diameter at the aperture (1/e <sup>2</sup> , mm)	~2.0	
Beam divergence, full angle (mrad)	<1.5	
Polarization ratio	>100:1 Horizontal ±5 degree (Vertical Optional)	
Warm-up time (minutes)	<10	
Pointing stability after warm-up (mrad)	<0.05	
Beam height from base plate (mm)	27.4	
Operating temperature (°C)	10~35	
Power supply (90-264VAC)	PSU-H-LED PSU-H-FDA	
Modulation option	TTL on/off, 1Hz-1KHz, 1KHz-10KHz, 10KHz-30KHz; and Analog modulation option	
Expected lifetime (hours)	10000	
Warranty	1 year	



**Note:** The laser head needs to be used on a heat sink with good heat dissipation.

MRL-FN-671	PSU-H-LED	PSU-H-FDA
<p>197(L)×70(W)×50(H) mm<sup>3</sup>, 2.0 kg</p>	<p>277 (L) ×145(W) ×106 (H) mm<sup>3</sup>, 2.6 kg</p>	<p>236(L) ×145(W) ×104(H) mm<sup>3</sup>, 2.3 kg</p>